

ReadySetGo 2.0 Notes:

The following material discusses features added to ReadySetGo 2.0 after the manual was printed. These notes will be incorporated in the next printing of the manual.

1. **Page Setup Dialog.** The ReadySetGo 2.0 disk contains a new version of the ImageWriter driver. The dialog which appears when Page Setup is selected is slightly different from the one shown on pages 5 and 87 of the manual. The new driver supports both the regular and 15 inch ImageWriters and it provides a 50 percent reduction option. Never use the Tall orientation with ReadySetGo. Always use either **Tall Adjusted** or **Wide**.

2. **“Other” Line Spacing.** The Format menu allows for, among other things, the selection of a line spacing for a text block. Page 79 of the manual refers to the choices of single, 1½ or double spacing. ReadySetGo 2.0 now supports the option of variable line spacing. To use this option select “Other” from the Format menu. A dialog will appear requesting a line spacing in points (there are 72 points in an inch). *All* text which appears in the active block, regardless of size, will display with this number of points separating the baseline of each line in the block. Sizes which are larger than the line spacing will appear “clipped” on the screen but output fine to the printer.

3. **Paragraph and Left Indent.** The Text Block Specification sheet presented when Modify is chosen while a text block is active contains the fields Para Indent and Left Indent. The Para Indent refers to the indentation of the first line of each paragraph from the left margin. It is given in inches from the left margin. The Left Indent refers to the indentation from the left margin of all lines of the paragraph *other* than the first. It also is given in inches from the left margin of the text block.

An alternative method of indenting paragraphs is to use the tab key. If *no tabs are set* the tab key inserts a fixed space of 8 points independent of the current size. This method of indentation must be used for text chains to avoid an unwanted indent when the first line of a text link comes from the middle of a paragraph. Indents larger than 8 points simply require hitting the tab key a few times.

4. **Fonts.** ReadySetGo 2.0 comes with a set of fonts installed. These fonts may be removed and/or others added using the font mover utility. ReadySetGo 2.0 automatically displays and makes available whichever fonts are resident in the System Folder.

5. **Laser Printer.** ReadySetGo 2.0 comes with the ImageWriter driver installed. To use ReadySetGo with Apple's laser printer follow the "laser installation" procedure described in the LaserWriter documentation.

6. **Switcher.** ReadySetGo 2.0 requires a 512K Macintosh. It will, though, work with Switcher providing you configure ReadySetGo with at least 256K.

7. **Limits.** The following limits apply to a ReadySetGo 2.0 document:

Maximum number of pages: 32 (Subject to memory limitations)

Maximum number of blocks per page: 100

Maximum number of blocks per document: 1,000

Maximum number of characters in a text block: 30K

Maximum number of characters in a text chain: 30K

8. **Product Support.** Product support is available from 1 pm to 5 pm (Eastern Standard Time) Monday through Friday. The telephone number is: 212-691-9114. In order to use our product support service you must be a **registered owner**.

9. **Backups.** The ReadySetGo 2.0 disk is not copy protected. Before you begin work use the Finder to make a backup copy of ReadySetGo.